

1 AZF 8403/K2/RS25

Cylinder Bed Shape, Overlock Machine with variable top feeder for attaching coller







Cylinder Bed Shape, Overlock Machine with variable top feeder for attaching coller

Numbering on Model



Sumbol of Series

② Class No.: 84= Cylinder Bed Overlock Machine

3 Submodel: 03= For single needle general seaming 20= For 2 needle general seaming

Needle distance : O= 1 needle, X= 2.0mm, Y=2.4mm

(5) Overlock width : 3=3nn, 4=4nn, 5=5nn

6 Feeding mode :

D= both positive & negative defferential available

Thape of knife:

F= flat knife A= angled knife

8 Devices : K2=automatic thread chain trimmer (vertical type · direct drive)

RS25 : labor saving device for attaching neckband

Submodels & Specifications

Model	Seam	ļ	۵	<u> - </u>	WŽ	<u>₩</u>	₹ !±	350	1, 100	<u>+</u>	Emer.
AZF8403	2	DC×27	3	-	3 4	1-22	*	10.8~12.3 • }	9	7	6,500
AZF8420		DC×27	4	2.0 2.4	4 5	1~3.2					6,500

RS25	Min.	Max.		
Circumfence of garments	400mm	1,050mm		
Width of 2-folded band	20mm	65mm		

With servo motor; needles can be rested at the upper dead point so that coller can be set on the right side of needle.

YAMATO SEWING MACHINE MFG.CO.,LTD. http://www.yamato-sewing.com

4-12, 4-CHOME, NISHI-TENMA, KITA-KU, OSAKA, 530-0047, JAPAN

TEL:+81-6-6364-5621 / FAX:+81-6-6364-7185 / E-mail:export-dept@yamato-sewing.com

YAMATO U.S.A. INC. TEL:+1-803-548-0334/FAX:+1-803-548-0405 YAMATO EUROPE GmbH.

TEL:+49-40-355347-0/FAX:+49-40-354371/E-mail:sales@yamato.de YAMATO (HONG KONG) CO., LTD. TEL:+852-2721-0251/FAX:+852-2723-0444/E-mail:yamato@yamato-sewing.com.hk

遭满挑(香港)有限公司 东莞代表处 TEL:+86-769-86231363/FAX:+86-769-86231362

大和嫌相机(宁波)有限公司 TEL:+86-574-86800518,86800558/FAX:+86-574-86800555/E-mail:marketing@yamato-china.com

大和维绍机制造株式会社 青岛事务所 TEL:+86-532-85783175/FAX:+86-532-85783172 大和镍钢机制造模式会社 上海事务所 TEL:+86.21.64400017.64400019/EAX:+86.21.64400021

YAMATO SINGAPORE PTE LTD. TEL:+65-6287-1955/FAX:+65-6287-1028/E-mail:sales@yamato-sewing.com.sg

M/S. YAMATO SINGAPORE PTE LTD., INDIA LIAISON OFFICE (TIRUPUR BRANCH). TEL:+91-421-4333701/FAX:+91-421-4333702/E-mail:yamato-sewing@airteibroadband.in

M/S. YAMATO SINGAPORE PTE LTD., INDIA LIAISON OFFICE (DELHI BRANCH) TEL:+91-11-41603280/FAX:+91-11-40574681

YAMATO SINGAPORE PTE LTD., CUSTOMER SERVICE CORRESPONDENT IN JAKARTA, INDONESIA FAX:+62-21-781-8727

YAMATO SINGAPORE PTE LTD., BANGLADESH LIAISON OFFICE TEL:+88-02-899-1864/FAX:+88-02-899-1865 TEL:+52-55-5764-9090/FAX:+52-55-5578-1470

THE RESIDENT REPRESENTATIVE OFFICE OF YAMATO SEWING MACHINE MFG. CO., LTD IN HO CHI MINH CITY TEL: +84-8-62969057/FAX; +84-8-38113384

The well-reputed AZF8400 type complete cylinder bed overlock machine with variable top feeder. There is no obstruction at all under and rear of cylinder bed so sewing tubular garment is smooth.

Moreover, combined with RS25 Device, it promises stable quality in the production of cuffs, neck & waist of T-shirts or sweat shirts - especially suitable for attaching collar.

YAMATO AZF8400

YAMATO AZF8400 has complete small cylinder bed (circumference: 151.5mm). Stitch length can be changed by pushbutton and differential feed amount by lever.


Moreover, movement of top feeder is correctly adjustable by Micro Adjuster.

The main advantage is that the top feeder is designed to draw complete ellipse just as bottom feeder does - with our unique direct drive mechanism. So no scratch by feed dog will be found on any thin and delicate material.



Full speed operation for any process

No need to reduce sewing speed even in top gathering or sewing heavy weight material.




YAMATO RS25 will satisfy you with uniform finish of collar.

YAMATO RS25 Device, with AZF8403/K2 or AZF8420/K2, will be a great help for operators in charge of attaching collars to T-shirts or sweat shirts.

RS25 allows you to:

- eliminate burst of seam as fabric holder guides fabric firmly.
- ② attach coller (waistband) in uniform width thanks to holder which folds them correctly in half.
- ③ finish band flatly, which enhances appearance & quality of garments.

Besides, AZF8403 or AZF8420 can attach small tubular bands to cuffs or ankles on the cylinder bed by swinging out the device.



Information on production (ex.)

(allowance rate:20%)

Production line	No. 1	No. 2	No. 3
Conventional coller attaching operation	32 sec.	44 sec.	39 sec.
	(900 pcs./8 hrs.)	(655 pcs./8 hrs.)	(738 pcs./8 hrs.)
YAMATO	28 sec.	32 sec.	35 sec.
AZF8403/K2/RS25	(1, 029 pcs./8 hrs.)	(900 pcs./8 hrs.)	(823 pcs./8 hrs.)
Save time	4 sec.	12 sec.	4 sec.
Productivity	114%	137%	112%
	(+129 pcs.)	(+245 pcs.)	(+85 pcs.)

Simple mechanism without electronics to open and close folder (patent pending).

RS25 includes air-operated holder (A) & (B), air-operated presser foot lifter (C), air-kit (D) for thread chain trimmer <K2>, and dust collector (E).

