"User Friendly" Optional Device


UTL Device: Automatic Under Thread Trimmer





* The anti-unraveling function has been proved as effective by Washing Test implemented by an accredited Japan National Laboratory.






UTL device cuts the under thread at two points of "A" and "B" as the left picture. As "C" becomes the thread end, it prevents the seam from unraveling, unlike the case of only "A" is cut at the end of the

- With easy handling, you will be satisfied with the seam finish in high quality, without worries about the seam unraveling.
- The device is housed inside without changing the design of Cylinder Bed. UTL can be installed in a machine equipped with UT device, no wasting of your present equipment.


WF Device

Walking Presserfoot Device





Walking Presserfoot can elimilate damage on fabric and present you "tunnel free" finish.



"Streamline" cylinder bed helps you enhancing productivity. It can be easily converted to other submodels for make, covering and tape attaching.

Ljamato

VC1790-8

2,3 Needle Cylinder Bed Interlock Stitch Machine

Numbering on Model

VC1790-156M-K4N-8F/UTL-A34F 1 234 567

- ① Symbol of Series ② Class No. ③ Number of Needle: 7=2,3 needles

- (5) Top Cover Thread Mechanism: 1=With Top Cover Thread
- Needle Distance: 32=3.2mm 40=4.0mm 48=4.8mm 56=5.6mm 64=6.4mm
- Shape of Stitch Tongue on Stitch Plate
- ® Covering Style 9 -8F=With Active Thread Control
- Device





Automatic Thread Trimmer											
	Under Thread Trimmer	Top Cover Thread Trimmer	Foot Lifter	Wiper	Anti-Unraveling Function	Air Type/ Solenoid Type					
UTL-A34F	•		•	•	•	Air Type					
UT-A34FC	•		•	•		Air Type					
UT-A34FC/ST2-AC	•	•	•			Sciencid Type					
UT-2C	•		•	•		Solenoid Type					
UT-4C/ST2-C	•	•	•			Solenoid Type					

Specification

Model	Seam Style	1	۵		뱦	<u> 114</u>	35	+	τĨ	Ö
VC1790-8F	Hemming Covering	UY128GAS 3 (2)	5 (4)	4.8 5.6 6.4	1.4~3.6	*	1:03~129	7.5 (MAX)	31	6,000 sti/min
VC1790-8F-SM (For Swimming Wear Use)	#	UY128GAS 3 (2)	5 (4)	3.2 4.0 4.8	1.4~3.6	*	1:03~129 ①	7.5 (MAX)	31 (33)	6,000 stilmin

^{*} It can make hemming and covering without changing parts. It can make tip over covering and binding by changing parts.

Specification and appearance on this catalog are subject to change For correct handling of products described on this catalog

TEL:+86-574-86800518,86800558/FAX:+86-574-86800555/E-mail:marketing@yamato-china.com YAMATO SEWING MACHINE MFG, OO., LTD. (HEAD OFFICE) TEL:+81-5-6364-5621/FAX:+85-6-364-7185/E-mail:export-dept@yamato-sewing.com

TEL:+1-803-548-0334/FAX:+1-803-548-0405

YAMATO EUROPE GmbH TEL:+49-40-355347-0/FAX:+49-40-354371/E-mail:sales@yamato.de

YAMATO (HONG KONG) CO., LTD. TEL:+852-2721-0251/FAX:+852-2723-0444/E-mail:yamato@yamato-sewing.com.hk

雅满稜(香港)有限公司 东莞代表处 TEL:+86-769-86231363/FAX:+86-769-86231362 大和雞奶机制造株式会社 青岛事务所 TEL:+86-532-85783175/FAX:+86-532-85783172 大和鍵纫机制造株式会社 上海事务所

YAMATO SINGAPORE PTE LTD. TEL:+65-6287-1955/FAX:+65-6287-1028/E-mail:sales@yamato-sewing.com.sg

YAMATO SINGAPORE PTE LTD, INDIA LIAISON OFFICE, TIRUPUR MAIN BRANCH TEL: +91-421-4333701/FAX: +91-421-4333702/E-mail:yamato-sewing@airtelbroadband.in

YAMATO SINGAPORE PTE LTD, INDIA LIAISON OFFICE, DELHI BRANCH TEL:++91-11-41603280/FAX:+91-11-41603281 YAMATO SINGAPORE PTELTD, CUSTOMER SERVICE CORRESPONDENT IN JAKARTA, INDONESIA Fax: +62-21-781-8727

YAMATO MEXICO OFFICE TEL:+52-55-5764-9090/FAX:+52-55-5578-1470

THE RESIDENT REPRESENTATIVE OFFICE OF YAMATO SEWING MACHINE MFG. CO., LTD IN HO CHI MINH CITY





1. Higher Efficiency

With conventional cylinder bed interlock machine, manual work for setting, feeding and removing are required due to its cylinder shape.





"Straight" fabric loading




Averagely, efficiency of covering on T-Shirt was enhanced over 20% by using VC1790!

The streamline shape of VC1790 helps smooth material flow during sewing circular items in cylinder. Less manual work is required for setting, feeding and removing. Also, operator can use his/her hands closer to needle drop point. So that stress-free handling is expected even when turning small circular work on the cylinder.

2. From Lightweight to Heavy Material

Switchable Needle Bar Stroke

Needle bar stroke can be switched from 31mm(standard) to 33mm by simply turning an eccentric pin on the needle bar. This epoch-making system shortens the downtime for conversion to meet extreme change of fabric weight.




Simple & Quick!




3. From Fleece to Microfiber

Active Thread Control (PAT.P)



Yamato's unique "Active Thread Control" is introduced to achieve incredible soft and elastic seam for microfiber!



Tunnel free finish for better appearance and comfort-to-wear garments.





Kind of seam can be changed from soft and elastic one to tightened one by simple and "visible" adjustment!




4. Non-Stain

"Non-Stain" technology brings you a solution for "Clean" finish & high efficiency. No oil, No worry!

Special seals prevents oil leakage. (PAT.P)









5. Easy Adjustment / Maintenance



Easy Threading and Trouble Free for Thread Winding around The Thread Take-up Cam


Easy threading by swing-up type looper thread take-up eyelet.

The special brush prevents the thread from winding around the looper thread take-up area.



New Foot Lifter Mechanism

The outer lever (similar to the one for overlock machine) enables easy assembling and adjustment of foot lifter with-out removing top cover.



Openable Side Cover Side cover is openable for easy feed dog height adjustment and cleaning.